



Eaton P005-006

Heavy-Duty PDU Power Cord, C13 to C14 -
15A, 250V, 14 AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P005-006
UPC	037332150004
PRODUCT LENGTH/DEPTH	11 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.78 lb
COMPLIANCES	RoHS REACH
CERTIFICATIONS	UL Listed cUL Listed CSA certified

INPUT CURRENT -MAX	15 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	UPS Network Switch Monitor/HDTV PDU Printer Router Server Computer
AWG-SIZE	14
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	9.3mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	2.08
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P005-006 Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 6-ft. (1.83 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	PDU-style cord replaces or upgrades standard power cord provided by manufacturer Thick 14 AWG wire gauge manages high power levels required for larger equipment 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet Lifetime limited warranty (Worldwide)

	Recommended for powering computers, servers and other network devices
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14
SIDEB CONNECTOR1	IEC-320-C13
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C13 C14
CONNECTOR	IEC 320-C14 IEC 320-C13

□□□□:
□□□□:
□□□:
□□: