



Eaton P005-010

Heavy-Duty PDU Power Cord, C13 to C14 -
15A, 250V, 14 AWG, 10 ft. (3.05 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series PDU power cord
CATALOG NUMBER	P005-010
UPC	037332140906
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	14.17 in
PRODUCT WIDTH	11.8 in
PRODUCT WEIGHT	1.05 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	cUL Listed CSA certified UL Listed

INPUT CURRENT -MAX	15 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Network Switch Printer Server UPS Monitor/HDTV Router Computer PDU
AWG-SIZE	14
CABLE LENGTH	10 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	9.3mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	2.08
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P005-010 Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 10-ft. (3.05 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	PDU-style cord replaces or upgrades standard power cord provided by manufacturer Recommended for powering computers, servers and other network devices Thick 14 AWG wire gauge manages high power levels required for larger equipment 10-ft. (3.05 m) length allows great flexibility in

	placing devices in relationship to AC outlet Lifetime limited warranty (Worldwide)
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14
SIDEB CONNECTOR1	IEC-320-C13
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C14 C13
CONNECTOR	IEC 320-C13 IEC 320-C14

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

