



## Eaton P005-18N

Heavy-Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 1.5 ft. (0.45 m), Black

□□□□

<b>PRODUCT NAME</b>	Eaton Tripp Lite series PDU power cord
<b>CATALOG NUMBER</b>	P005-18N
<b>UPC</b>	037332155931
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	10 in
<b>PRODUCT WIDTH</b>	7.1 in
<b>PRODUCT WEIGHT</b>	0.28 lb
<b>COMPLIANCES</b>	RoHS REACH
<b>CERTIFICATIONS</b>	UL Listed cUL Listed CSA certified



Powering Business Worldwide



<b>INPUT CURRENT -MAX</b>	15 Ampere
<b>OPERATING TEMPERATURE RANGE</b>	-4° to 140°F (-20° to 60°C)
<b>STORAGE TEMPERATURE</b>	-4° to 140°F (-20° to 60°C)
<b>DEVICE COMPATIBILITY</b>	Server Monitor/HDTV UPS Network Switch Printer Router PDU Computer
<b>AWG-SIZE</b>	14
<b>CABLE LENGTH</b>	1.5 Foot
<b>NUMBER OF CONDUCTORS</b>	3
<b>OPERATING HUMIDITY</b>	20% to 80% RH
<b>OUTER CABLE DIAMETER</b>	9.2mm
<b>POWER CORD JACKET TYPE</b>	SJT
<b>STORAGE HUMIDITY RANGE</b>	20% to 80% RH
<b>WIRE SIZE (AWG) - MAX</b>	2.08
<b>CABLE LENGTH RANGE</b>	Up to 4ft (up to 1M)
<b>CABLE JACKET RATING</b>	FT2
<b>CABLE JACKET COLOR</b>	Black
<b>PACKAGE CONTENTS</b>	P005-18N Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 1.5 ft., Black
<b>CONNECTOR COLOR</b>	Black
<b>CONNECTOR TYPE</b>	Power
<b>PRODUCT FEATURES</b>	High Voltage
<b>CABLE JACKET MATERIAL</b>	PVC
<b>CONNECTOR STYLE</b>	Straight
<b>PRODUCT HIGHLIGHTS</b>	1.5 ft. length allows flexibility in placing devices, while avoiding cable clutter Thick 14 AWG wire gauge manages high power levels required for larger equipment Recommended for powering computers, servers and other network devices PDU-style cord replaces or upgrades standard power



