



Eaton P006-006-13LA

Computer Power Cord, NEMA 5-15P to Left-Angle C13 - 10A, 125V, 18 AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P006-006-13LA
UPC	037332156464
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS
CERTIFICATIONS	cUL Listed UL Listed

INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	UPS Computer Monitor/HDTV PDU Printer Server
AWG-SIZE	18
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	7.8mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P006-006-13LA NEMA 5-15P to Left-Angle C13 Power Extension Cable, 6-ft. (1.83 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	Angled Plug
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Angled
PRODUCT HIGHLIGHTS	Recommended for powering computers, printers and other compatible peripherals Adds 6-ft. (1.83 m) to your existing power connection to provide flexibility in placing devices Lifetime limited warranty (Worldwide) Ideal replacement for worn-out or missing computer power cord Left-angle C13 plug allows easier connection in confined or hard-to-reach

	spaces NEMA 5-15P plug connects to AC power; C13 plug connects to device's C14 inlet
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA 5-15P
SIDEB CONNECTOR1	IEC-320-C13 - LEFT ANGLE
VOLTAGE RATING	125 VAC
CONNECTOR GROUP	C13 5-15P
CONNECTOR	IEC 320-C13 left angle NEMA 5-15P
