




Eaton P006-006-515MF

Piggyback Extension Cord, NEMA 5-15P/5-15R to C13 - 13A, 125V, 16 AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P006-006-515MF
UPC	037332167781
PRODUCT LENGTH/DEPTH	4.7 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

□□□□	
INPUT CURRENT -MAX	13 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	UPS Server Monitor/HDTV Printer Computer PDU
AWG-SIZE	16
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	20% to 80% RH
OUTER CABLE DIAMETER	9mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	20% to 80% RH
WIRE SIZE (AWG) - MAX	1.31
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P006-006-515MF Piggyback Extension Cord, 6-ft. (1.83 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Combination 5-15P/5-15R connector allows a second 5-15P cord to plug into it Ideal replacement for a worn-out or missing piggyback extension cord Lifetime limited warranty (Worldwide) Recommended for powering dual computers, monitors or other compatible peripherals 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA 5-15P



SIDE B CONNECTOR1	NEMA 5-15R IEC-320-C13
VOLTAGE RATING	125 VAC
SIDE A CONNECTOR2	NEMA 5-15R
CONNECTOR GROUP	C13 5-15R 5-15P
CONNECTOR	NEMA 5-15P IEC 320-C13 NEMA 5-15R
