



Eaton P006-010

Desktop Computer AC Power Cable, NEMA 5-15P to C13 - 10A, 125V, 18 AWG, 10 ft. (3.05 m), Black

Specifications

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P006-010
UPC	037332164780
PRODUCT LENGTH/DEPTH	0.1 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.72 lb
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

□□□□	
INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Printer Server UPS Monitor/HDTV Computer PDU
AWG-SIZE	18
CABLE LENGTH	10 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	7.8mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P006-010 NEMA 5-15P to C13 Computer Power Cable, 10-ft. (3.05 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet NEMA 5-15P to C13 extension cord is ideal replacement for worn-out or missing cable Lifetime limited warranty (Worldwide) Recommended for powering computers, printers and other home/office peripherals
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA 5-15P
SIDEB CONNECTOR1	IEC-320-C13



