




Eaton P010-012

Desktop Computer Power Cable, NEMA 5-15P to C13 - 10A, 125V, 18 AWG, 12 ft. (3.66 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P010-012
UPC	037332013415
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	0.86 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	cUL Listed UL Listed

□□□□	
INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Computer PDU Printer UPS Monitor/HDTV Server
AWG-SIZE	18
CABLE LENGTH	12 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	6.3mm
POWER CORD JACKET TYPE	SVT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P010-012 NEMA 5-15P to C13 Computer Power Cable, 12-ft. (3.66 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	12-ft. (3.66 m) length allows great flexibility in placing devices in relationship to AC outlet Recommended for powering computers, printers and other home/office peripherals Ideal replacement for a worn-out or missing NEMA 5-15P to C13 cable Lifetime limited warranty (Worldwide)
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA 5-15P
SIDEB CONNECTOR1	IEC-320-C13
VOLTAGE RATING	125 VAC



CONNECTOR GROUP	C13 5-15P
CONNECTOR	IEC 320-C13 NEMA 5-15P
