



Eaton P012

Eaton Moeller series White moulded range (PREMERA) - Wiring Devices. Switch, 10A, 2G, 1-way

□□□□

PRODUCT NAME	Eaton Moeller series White moulded range (PREMERA) - Wiring devices
CATALOG NUMBER	P012
PRODUCT LENGTH/DEPTH	27 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	0.082 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	BS EN 60669-1 IEC 60669-1



Powering Business Worldwide

□□□□

FEATURES	Push button switch Halogen free
SURFACE FINISHING	Matt
SPECIAL FEATURES	Zinc Coated Steel with clear Passivation
TYPE	Premera White Moulded Switches
AMPERAGE RATING	10 AX
VOLTAGE RATING	250 V AC
CONTACT MATERIAL	Nickel Silver
HEAD STYLE	Slotted head
ILLUMINATION	No
SURFACE PROTECTION	Untreated
MATERIAL QUALITY	Thermoplastic
ASSEMBLY ARRANGEMENT	Basic element with full cover plate
BASE COLOR	Gray
BASE MATERIAL	Thermoplastic
TERMINAL MATERIAL	Brass
BUILT-IN DEPTH	25 mm
BUILT-IN INSTALLATION BOX DEPTH - MIN	25 mm
NOMINAL VOLTAGE - MAX	240 V
NUMBER OF MODULES (MODULE SYSTEM)	0
NUMBER OF ROCKERS	2
SWITCH TYPE	1 Way
MOUNTING METHOD	Flush mounted (plaster)
DEGREE OF PROTECTION	IP3X IP20
FASTENING TYPE	Screw mounting
NUMBER OF GANGS	2
FIXING CENTERS	60.3 mm
FRONT PLATE COLOR/FINISHING	White
MATERIAL	Plastic Urea
FRONT PLATE DEPTH	9 mm
FRONT PLATE MATERIAL	Urea
FRONT PLATE/MODULE DIMENSIONS	86 mm x 86 mm
WIRING SYSTEM	Off switch 1-pole

□□

	eaton-british-standard-wiring-accessories-poster-en-uk.pdf
□□□□	eaton-premera-mix-specification-guide-product-aid-pa081001en-en-gb.pdf
□□□□	eaton-wiring-accessories-and-single-phase-distribution-pg00400018u-en-gb.pdf

