



Eaton P013-006

3-Slot Power Cord, NEMA 5-15P to C5 - Laptop/Notebook, 7A, 125V, 18 AWG, 6 ft. (1.8 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P013-006
UPC	037332164810
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	8.86 in
PRODUCT WIDTH	12.8 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed



Powering Business Worldwide



INPUT CURRENT -MAX	7 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	UPS Computer Laptop Monitor/HDTV PDU Projector
AWG-SIZE	18
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	6.3mm
POWER CORD JACKET TYPE	SVT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	0.82
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P013-006 3-Slot Power Cord, NEMA 5-15P to C5 - 6 ft. (1.8 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Ideal replacement for a worn-out or missing laptop power cable Recommended for powering notebook computers and laptops with C6 inlets 6 ft. length allows flexibility in placing devices in relationship to AC outlet
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA 5-15P
SIDEB CONNECTOR1	IEC-320-C5
VOLTAGE RATING	125 VAC
CONNECTOR GROUP	C5

