



Eaton P018-006

Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P018-006
UPC	037332168443
PRODUCT LENGTH/DEPTH	11 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.76 lb
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

□□□□	
INPUT CURRENT -MAX	15 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Network Switch UPS PDU
AWG-SIZE	14
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	9.3mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	2.08
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	6-ft. C14 to C15 Power Cord
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	100-250V, 15A, 14AWG, SJT UL Listed Lifetime limited warranty (Worldwide) 6-ft. heavy-duty power cord, C14-to-C15
PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C14
SIDEB CONNECTOR1	IEC-320-C15
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C13 C15
CONNECTOR	IEC 320-C14 IEC 320-C15

□□
