



Eaton P023-001

Heavy-Duty Power Extension Cable, NEMA L5-15R to NEMA 5-15P - 15A, 120V, 14 AWG, 1 ft. (0.31 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P023-001
UPC	037332145567
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

P023-001	
INPUT CURRENT -MAX	15 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Server UPS PDU Computer Monitor/HDTV
AWG-SIZE	14
CABLE LENGTH	1 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	20% to 80% RH
OUTER CABLE DIAMETER	9.2mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	20% to 80% RH
WIRE SIZE (AWG) - MAX	2.08
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P023-001 Heavy-Duty Extension Cable, L5-15R to 5-15P, 1-ft. (0.31 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Recommended for powering computers, servers and other network devices Heavy-duty cord replaces or upgrades standard power cord provided by manufacturer Lifetime limited warranty (Worldwide) 1-ft. (0.31 m) length allows flexibility in placing devices, while avoiding cable clutter Thick 14 AWG wire gauge manages high power levels required for larger equipment



