



Eaton P032-E02

PDU Power Cord, C13 to P-Lock Lite C20 - 15A, 100-250V, 14 AWG, 2 ft. (0.6 m), Black



PRODUCT NAME	Eaton Tripp Lite series P-Lock power cord
CATALOG NUMBER	P032-E02
UPC	037332295309
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12.8 in
PRODUCT WIDTH	8.9 in
PRODUCT WEIGHT	0.32 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	CSA C22.2. UL Listed cUL Listed



Powering Business Worldwide



INPUT CURRENT -MAX	15 Ampere
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
RELATIVE HUMIDITY	35 TO 85% RH, Non-Condensing
STORAGE TEMPERATURE	23° to 158°F (-5° to 70°C)
DEVICE COMPATIBILITY	Computer Monitor/HDTV PDU Printer Server Tablet UPS
AWG-SIZE	14
CABLE LENGTH	2 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	9.3mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	2.08
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P032-E02 PDU Power Cord, C13 to P-Lock Lite C20, 2 ft. (0.6 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage Locking Plug
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Recommended for powering computers, servers and other network devices P-Lock Lite C20 connector eliminates accidental cable disconnections in a crowded PDU 2 ft. length allows flexibility in mounting devices within a rack while avoiding cable clutter PDU-style cord replaces or upgrades non-locking

