



Eaton P032-E04

PDU Power Cord, C13 to P-Lock Lite C20 - 15A, 100-250V, 14 AWG, 4 ft. (1.2 m), Black

□□□□

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Tripp Lite series P-Lock power cord |
| CATALOG NUMBER | P032-E04 |
| UPC | 037332295316 |
| PRODUCT LENGTH/DEPTH | 0.5 in |
| PRODUCT HEIGHT | 12.8 in |
| PRODUCT WIDTH | 8.9 in |
| PRODUCT WEIGHT | 0.49 lb |
| COMPLIANCES | REACH RoHS |
| CERTIFICATIONS | CSA C22.2. UL Listed cUL Listed |



Powering Business Worldwide



| | |
|------------------------------------|---|
| INPUT CURRENT -MAX | 15 Ampere |
| OPERATING TEMPERATURE RANGE | 14° to 140°F (-10° to 60°C) |
| RELATIVE HUMIDITY | 35 TO 85% RH, Non-Condensing |
| STORAGE TEMPERATURE | 23° to 158°F (-5° to 70°C) |
| DEVICE COMPATIBILITY | Computer Monitor/HDTV PDU Printer Server Tablet UPS |
| AWG-SIZE | 14 |
| CABLE LENGTH | 4 Foot |
| NUMBER OF CONDUCTORS | 3 |
| OPERATING HUMIDITY | 10% to 65% RH |
| OUTER CABLE DIAMETER | 9.3mm |
| POWER CORD JACKET TYPE | SJT |
| STORAGE HUMIDITY RANGE | 10% to 65% RH |
| WIRE SIZE (AWG) - MAX | 2.08 |
| CABLE JACKET RATING | VW-1 |
| CABLE JACKET COLOR | Black |
| PACKAGE CONTENTS | P032-E04 PDU Power Cord, C13 to P-Lock Lite C20, 4 ft. (1.2 m), Black |
| CONNECTOR COLOR | Black |
| CONNECTOR TYPE | Power |
| PRODUCT FEATURES | High Voltage Locking Plug |
| CABLE JACKET MATERIAL | PVC |
| PRODUCT HIGHLIGHTS | Recommended for powering computers, servers and other network devices P-Lock Lite C20 connector eliminates accidental cable disconnections in a crowded PDU 4 ft. length allows flexibility in mounting devices within a rack while avoiding cable clutter PDU-style cord replaces or upgrades non-locking power cable provided by |

