




Eaton P036-002

Power Extension Cord, C19 to C20 - Heavy-Duty, 20A, 250V, 12 AWG, 2 ft. (0.61 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P036-002
UPC	037332141613
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12.8 in
PRODUCT WIDTH	8.9 in
PRODUCT WEIGHT	0.55 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

□□□□	
INPUT CURRENT -MAX	20 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Server Router UPS Network Switch PDU
AWG-SIZE	12
CABLE LENGTH	2 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	11mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	3.31
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P036-002 C19 to C20 Heavy-Duty Extension Cord, 2-ft. (0.61 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter Recommended for powering servers, routers and other high-output network devices Lifetime limited warranty (Worldwide) C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer Thick 12 AWG wire gauge manages high power levels required for larger equipment



PLUG COLOR	Black
SIDEA CONNECTOR1	IEC-320-C20
SIDEB CONNECTOR1	IEC-320-C19
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C19 C20
CONNECTOR	IEC 320-C19 IEC 320-C20
