



Eaton P036-006

Power Extension Cord, C19 to C20 - Heavy-Duty, 20A, 250V, 12 AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P036-006
UPC	037332141620
PRODUCT LENGTH/DEPTH	11 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	1.02 lb
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

Specifications		Features	
INPUT CURRENT -MAX	20 Ampere		
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)		
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)		
DEVICE COMPATIBILITY	Server UPS Router Network Switch PDU		
AWG-SIZE	12		
CABLE LENGTH	6 Foot		
NUMBER OF CONDUCTORS	3		
OPERATING HUMIDITY	10% to 65% RH		
OUTER CABLE DIAMETER	11mm		
POWER CORD JACKET TYPE	SJT		
STORAGE HUMIDITY RANGE	10% to 65% RH		
WIRE SIZE (AWG) - MAX	3.31		
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)		
CABLE JACKET RATING	VW-1		
CABLE JACKET COLOR	Black		
PACKAGE CONTENTS	P036-006 C19 to C20 Heavy-Duty Extension Cord, 6-ft. (1.83 m), Black		
CONNECTOR COLOR	Black		
CONNECTOR TYPE	Power		
PRODUCT FEATURES	High Voltage		
CABLE JACKET MATERIAL	PVC		
CONNECTOR STYLE	Straight		
PRODUCT HIGHLIGHTS	C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer Recommended for powering servers, routers and other high-output network devices Thick 12 AWG wire gauge manages high power levels required for larger equipment 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet Lifetime limited warranty (Worldwide)		

