



Eaton P036-010

Power Extension Cord, C19 to C20 - Heavy-Duty, 20A, 250V, 12 AWG, 10 ft. (3.05 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P036-010
UPC	037332176837
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10.98 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	1.62 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

□□□□	
INPUT CURRENT -MAX	20 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
RELATIVE HUMIDITY	10% to 65% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Router UPS Network Switch PDU Server
AWG-SIZE	12
CABLE LENGTH	10 Foot
NUMBER OF CONDUCTORS	3
OUTER CABLE DIAMETER	11mm
POWER CORD JACKET TYPE	SJT
WIRE SIZE (AWG) - MAX	3.31
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P036-010 C19 to C20 Heavy-Duty Extension Cord, 10-ft. (3.05 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer Recommended for powering servers, routers and other high-output network devices 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet Thick 12 AWG wire gauge manages high power levels required for larger equipment Lifetime limited warranty (Worldwide)

□□	
----	--

