




Eaton P040-006

Power Cord, C19 to NEMA L6-20 - Heavy-Duty, 20A, 250V, 12 AWG, 6 ft. (1.83 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P040-006
UPC	037332164902
PRODUCT LENGTH/DEPTH	7.8 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	6 in
PRODUCT WEIGHT	0.8 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

Specifications	
INPUT CURRENT -MAX	20 Ampere
OPERATING TEMPERATURE RANGE	-4° to 194°F (-20° to 90°C)
STORAGE TEMPERATURE	-4° to 194°F (-20° to 90°C)
DEVICE COMPATIBILITY	Router Network Switch Server UPS PDU
AWG-SIZE	12
CABLE LENGTH	6 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	20% to 70% RH
OUTER CABLE DIAMETER	11mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	20% to 80% RH
WIRE SIZE (AWG) - MAX	3.31
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P040-006 C19 to L6-20P Power Cord, 6-ft. (1.83 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage Locking Plug
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	C19 to L6-20P power cord is ideal replacement for worn-out or missing cable L6-20 locking connector maintains secure link to avoid loss of power and costly downtime Recommended for powering servers, switches and other essential network devices Thick 12 AWG wire gauge manages high power levels required for larger equipment Long 6-ft. (1.83 m) cord provides flexibility in



	placing connected device away from outlet Lifetime limited warranty (Worldwide)
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA L6-20P
SIDEB CONNECTOR1	IEC-320-C19
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C19 L6-20P
CONNECTOR	IEC 320-C19 NEMA L6-20P



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

