




## Eaton P040-012

Power Cord, C19 to NEMA L6-20 - Heavy-Duty, 20A, 250V, 12 AWG, 12 ft. (3.66 m), Black

□□□□

|                             |                                    |
|-----------------------------|------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Tripp Lite series power cord |
| <b>CATALOG NUMBER</b>       | P040-012                           |
| <b>UPC</b>                  | 037332180681                       |
| <b>PRODUCT LENGTH/DEPTH</b> | 0.1 in                             |
| <b>PRODUCT HEIGHT</b>       | 7.1 in                             |
| <b>PRODUCT WIDTH</b>        | 7.9 in                             |
| <b>PRODUCT WEIGHT</b>       | 2.2 lb                             |
| <b>WARRANTY</b>             | Limited lifetime                   |
| <b>COMPLIANCES</b>          | RoHS                               |
| <b>CERTIFICATIONS</b>       | UL Listed<br>cUL Listed            |

| <div> <div></div> <div></div> <div></div> <div></div> </div> |                                                                                                                                                                                                                                                                                                                                                                                              |
|--------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| INPUT CURRENT -MAX                                           | 20 Ampere                                                                                                                                                                                                                                                                                                                                                                                    |
| OPERATING TEMPERATURE RANGE                                  | 23° to 140°F (-5° to 60°C)                                                                                                                                                                                                                                                                                                                                                                   |
| STORAGE TEMPERATURE                                          | -4° to 176°F (-20° to 80°C)                                                                                                                                                                                                                                                                                                                                                                  |
| DEVICE COMPATIBILITY                                         | Router<br>Server<br>UPS<br>Network Switch<br>PDU                                                                                                                                                                                                                                                                                                                                             |
| AWG-SIZE                                                     | 12                                                                                                                                                                                                                                                                                                                                                                                           |
| CABLE LENGTH                                                 | 12 Foot                                                                                                                                                                                                                                                                                                                                                                                      |
| NUMBER OF CONDUCTORS                                         | 3                                                                                                                                                                                                                                                                                                                                                                                            |
| OPERATING HUMIDITY                                           | 0% to 90% RH, Non-Condensing                                                                                                                                                                                                                                                                                                                                                                 |
| OUTER CABLE DIAMETER                                         | 11.2mm                                                                                                                                                                                                                                                                                                                                                                                       |
| POWER CORD JACKET TYPE                                       | SJT                                                                                                                                                                                                                                                                                                                                                                                          |
| STORAGE HUMIDITY RANGE                                       | 0% to 90% RH, Non-Condensing                                                                                                                                                                                                                                                                                                                                                                 |
| WIRE SIZE (AWG) - MAX                                        | 3.31                                                                                                                                                                                                                                                                                                                                                                                         |
| CABLE LENGTH RANGE                                           | 9 - 14ft (2 - 4M)                                                                                                                                                                                                                                                                                                                                                                            |
| CABLE JACKET RATING                                          | VW-1                                                                                                                                                                                                                                                                                                                                                                                         |
| CABLE JACKET COLOR                                           | Black                                                                                                                                                                                                                                                                                                                                                                                        |
| PACKAGE CONTENTS                                             | P040-012 C19 to L6-20P Power Cord, 12-ft. (3.66 m), Black                                                                                                                                                                                                                                                                                                                                    |
| CONNECTOR COLOR                                              | Black                                                                                                                                                                                                                                                                                                                                                                                        |
| CONNECTOR TYPE                                               | Power                                                                                                                                                                                                                                                                                                                                                                                        |
| PRODUCT FEATURES                                             | Locking Plug<br>High Voltage                                                                                                                                                                                                                                                                                                                                                                 |
| CABLE JACKET MATERIAL                                        | PVC                                                                                                                                                                                                                                                                                                                                                                                          |
| CONNECTOR STYLE                                              | Straight                                                                                                                                                                                                                                                                                                                                                                                     |
| PRODUCT HIGHLIGHTS                                           | <p>Recommended for powering servers, switches and other essential network devices</p> <p>Thick 12 AWG wire gauge manages high power levels required for larger equipment</p> <p>Lifetime limited warranty (Worldwide)</p> <p>C19 to L6-20P power cord is ideal replacement for worn-out or missing cable</p> <p>L6-20 Locking connector maintains secure link to avoid loss of power and</p> |



|                  |                                                                                                                               |
|------------------|-------------------------------------------------------------------------------------------------------------------------------|
|                  | costly downtime<br>Extra-long 12-ft. (3.66 m)<br>cord provides flexibility in<br>placing connected device<br>away from outlet |
| PLUG COLOR       | Black                                                                                                                         |
| SIDEA CONNECTOR1 | NEMA L6-20P                                                                                                                   |
| SIDEB CONNECTOR1 | IEC-320-C19                                                                                                                   |
| VOLTAGE RATING   | 250 VAC                                                                                                                       |
| CONNECTOR GROUP  | C19<br>L6-20P                                                                                                                 |
| CONNECTOR        | IEC 320-C19<br>NEMA L6-20P                                                                                                    |

|  |
|--|
|  |
|  |
|  |
|  |