



Eaton P040-014

Power Cord, C19 to NEMA L6-20 - Heavy-Duty, 20A, 250V, 12 AWG, 14 ft. (4.27 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P040-014
UPC	037332164933
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	2.4 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	UL Listed cUL Listed

□□□□	
INPUT CURRENT -MAX	20 Ampere
OPERATING TEMPERATURE RANGE	-4° to 194°F (-20° to 90°C)
STORAGE TEMPERATURE	-4° to 194°F (-20° to 90°C)
DEVICE COMPATIBILITY	PDU Router UPS Network Switch Server
AWG-SIZE	12
CABLE LENGTH	14 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	20% to 70% RH
OUTER CABLE DIAMETER	11mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	20% to 80% RH
WIRE SIZE (AWG) - MAX	3.31
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P040-014 C19 to L6-20P Power Cord, 14-ft. (4.27 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage Locking Plug
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) C19 to L6-20P power cord is ideal replacement for worn-out or missing cable Thick 12 AWG wire gauge manages high power levels required for larger equipment Recommended for powering servers, switches and other essential network devices L-60 locking connector maintains secure link to avoid loss of power and costly downtime
□□	

	Extra-long 14-ft. (4.27 m) cord provides flexibility in placing connected device away from outlet
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA L6-20P
SIDEB CONNECTOR1	IEC-320-C19
VOLTAGE RATING	100 - 250 VAC
CONNECTOR GROUP	C19 L6-20P
CONNECTOR	NEMA L6-20P IEC 320-C19



Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

