




Eaton P044-06I

Power Cord Adapter, NEMA L5-20R to NEMA 5-20P - Heavy-Duty, 20A, 120V, 12 AWG, 8.66-in. (21.99 cm), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P044-06I
UPC	037332139115
PRODUCT LENGTH/DEPTH	0.1 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS
CERTIFICATIONS	cUL Listed UL Listed

SPECIFICATIONS	
INPUT CURRENT -MAX	20 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Server UPS PDU
AWG-SIZE	12
CABLE LENGTH	0.72 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	11mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	3.31
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P044-06I L5-20R to 5-20P Heavy-Duty Power Adapter, 8.66 in., Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Locking connector maintains secure link to avoid loss of power and costly downtime Lifetime limited warranty (Worldwide) 8.66 in. adapter allows easy transition to L5-20R outlet with no electrician needed Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer Thick 12 AWG wire gauge manages high power levels required for larger equipment
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA 5-20P



SIDE B CONNECTOR1	NEMA L5-20R
VOLTAGE RATING	125 VAC
CONNECTOR GROUP	5-20P L5-20R
CONNECTOR	NEMA 5-20P NEMA L5-20R



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

