




Eaton P045-010

Power Cord, C19 to NEMA L5-20P - Heavy-Duty, 20A, 125V, 12 AWG, 10 ft. (3.05 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P045-010
UPC	037332140937
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10.98 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	1.72 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	cUL Listed UL Listed

□□□□	
INPUT CURRENT -MAX	20 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
RELATIVE HUMIDITY	10% to 65% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	PDU Server UPS
AWG-SIZE	12
CABLE LENGTH	10 Foot
NUMBER OF CONDUCTORS	3
OUTER CABLE DIAMETER	11mm
POWER CORD JACKET TYPE	SJT
WIRE SIZE (AWG) - MAX	3.31
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P045-010 C19 to L5-20P Heavy-Duty Extension Cord, 10-ft. (3.05 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Thick 12 AWG wire gauge manages high power levels required for larger equipment Locking connector maintains secure link to avoid loss of power and costly downtime Lifetime limited warranty (Worldwide) Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA L5-20P



SIDE B CONNECTOR1	IEC-320-C19
VOLTAGE RATING	125 VAC
CONNECTOR GROUP	L5-20P C19
CONNECTOR	NEMA L5-20P IEC 320-C19



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

