



## Eaton P047-006

Power Cord, C19 to C14 - Heavy-Duty, 15A, 250V, 14 AWG, 6 ft. (1.83 m), Black



<b>PRODUCT NAME</b>	Eaton Tripp Lite series power cord
<b>CATALOG NUMBER</b>	P047-006
<b>UPC</b>	037332150059
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	12.8 in
<b>PRODUCT WIDTH</b>	8.9 in
<b>PRODUCT WEIGHT</b>	0.8 lb
<b>COMPLIANCES</b>	RoHS
<b>CERTIFICATIONS</b>	UL Listed cUL Listed



Powering Business Worldwide



<b>INPUT CURRENT -MAX</b>	15 Ampere
<b>OPERATING TEMPERATURE RANGE</b>	-4° to 140°F (-20° to 60°C)
<b>STORAGE TEMPERATURE</b>	-4° to 140°F (-20° to 60°C)
<b>DEVICE COMPATIBILITY</b>	UPS PDU Server Computer
<b>AWG-SIZE</b>	14
<b>CABLE LENGTH</b>	6 Foot
<b>NUMBER OF CONDUCTORS</b>	3
<b>OPERATING HUMIDITY</b>	10% to 65% RH
<b>OUTER CABLE DIAMETER</b>	9.3mm
<b>POWER CORD JACKET TYPE</b>	SJT
<b>STORAGE HUMIDITY RANGE</b>	10% to 65% RH
<b>WIRE SIZE (AWG) - MAX</b>	2.08
<b>CABLE LENGTH RANGE</b>	5 - 8ft (1 - 2M)
<b>CABLE JACKET RATING</b>	VW-1
<b>CABLE JACKET COLOR</b>	Black
<b>PACKAGE CONTENTS</b>	P047-006 C19 to C14 Power Cord, 6-ft. (1.83 m), Black
<b>CONNECTOR COLOR</b>	Black
<b>CONNECTOR TYPE</b>	Power
<b>PRODUCT FEATURES</b>	High Voltage
<b>CABLE JACKET MATERIAL</b>	PVC
<b>CONNECTOR STYLE</b>	Straight
<b>PRODUCT HIGHLIGHTS</b>	Thick 14 AWG wire gauge manages high power levels required for larger equipment 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet C19 to C14 cable for powering computers, servers and other network devices Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer
<b>PLUG COLOR</b>	Black
<b>SIDEA CONNECTOR1</b>	IEC-320-C14

