



Eaton P047-010

Power Cord, C19 to C14 - Heavy-Duty, 15A, 250V, 14 AWG, 10 ft. (3.05 m), Black



| | |
|-----------------------------|------------------------------------|
| PRODUCT NAME | Eaton Tripp Lite series power cord |
| CATALOG NUMBER | P047-010 |
| UPC | 037332140890 |
| PRODUCT LENGTH/DEPTH | 0.5 in |
| PRODUCT HEIGHT | 12.8 in |
| PRODUCT WIDTH | 8.9 in |
| PRODUCT WEIGHT | 1.1 lb |
| COMPLIANCES | RoHS |
| CERTIFICATIONS | UL Listed cUL Listed |



Powering Business Worldwide



| | |
|------------------------------------|--|
| INPUT CURRENT -MAX | 15 Ampere |
| OPERATING TEMPERATURE RANGE | -4° to 140°F (-20° to 60°C) |
| STORAGE TEMPERATURE | -4° to 140°F (-20° to 60°C) |
| DEVICE COMPATIBILITY | Server UPS Computer PDU |
| AWG-SIZE | 14 |
| CABLE LENGTH | 10 Foot |
| NUMBER OF CONDUCTORS | 3 |
| OPERATING HUMIDITY | 10% to 65% RH |
| OUTER CABLE DIAMETER | 9.3mm |
| POWER CORD JACKET TYPE | SJT |
| STORAGE HUMIDITY RANGE | 10% to 65% RH |
| WIRE SIZE (AWG) - MAX | 2.08 |
| CABLE LENGTH RANGE | 9 - 14ft (2 - 4M) |
| CABLE JACKET RATING | VW-1 |
| CABLE JACKET COLOR | Black |
| PACKAGE CONTENTS | P047-010 C19 to C14 Power Cord, 10-ft. (3.05 m), Black |
| CONNECTOR COLOR | Black |
| CONNECTOR TYPE | Power |
| PRODUCT FEATURES | High Voltage |
| CABLE JACKET MATERIAL | PVC |
| CONNECTOR STYLE | Straight |
| PRODUCT HIGHLIGHTS | Thick 14 AWG wire gauge manages high power levels required for larger equipment C19 to C14 cable for powering computers, servers and other network devices 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer |
| PLUG COLOR | Black |
| SIDEA CONNECTOR1 | IEC-320-C14 |

