



## Eaton P060-006

UK Computer Power Cord - BS1363 to C5,  
2.5A, 250V, 18 AWG, 6 ft. (1.83 m), Black

□□□□

<b>PRODUCT NAME</b>	Eaton Tripp Lite series power cord
<b>CATALOG NUMBER</b>	P060-006
<b>UPC</b>	037332153630
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	9.06 in
<b>PRODUCT WIDTH</b>	7.09 in
<b>PRODUCT WEIGHT</b>	0.43 lb
<b>COMPLIANCES</b>	REACH RoHS
<b>CERTIFICATIONS</b>	cUL Listed UL Listed CSA certified



Powering Business Worldwide



<b>OPERATING TEMPERATURE RANGE</b>	-4° to 140°F (-20° to 60°C)
<b>STORAGE TEMPERATURE</b>	-4° to 140°F (-20° to 60°C)
<b>DEVICE COMPATIBILITY</b>	UPS Computer PDU Laptop
<b>AWG-SIZE</b>	18
<b>CABLE LENGTH</b>	6 Foot
<b>NUMBER OF CONDUCTORS</b>	3
<b>OPERATING HUMIDITY</b>	20% to 70% RH
<b>OUTER CABLE DIAMETER</b>	6.5mm
<b>POWER CORD JACKET TYPE</b>	H05VV-F
<b>STORAGE HUMIDITY RANGE</b>	20% to 80% RH
<b>WIRE SIZE (AWG) - MAX</b>	0.82
<b>CABLE LENGTH RANGE</b>	5 - 8ft (1 - 2M)
<b>CABLE JACKET RATING</b>	H05VV-F
<b>CABLE JACKET COLOR</b>	Black
<b>PACKAGE CONTENTS</b>	P060-006 BS1363 to C5 UK Computer Power Cable, 6 ft. (1.8 m), Black
<b>CONNECTOR TYPE</b>	Power
<b>PRODUCT FEATURES</b>	High Voltage
<b>CABLE JACKET MATERIAL</b>	PVC
<b>PRODUCT HIGHLIGHTS</b>	6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet UK computer power cable for powering notebooks and laptops with C6 inlets Ideal replacement for worn-out or missing UK IEC power cord
<b>PLUG COLOR</b>	Black
<b>SIDEA CONNECTOR1</b>	BS1363 UK PLUG
<b>SIDEB CONNECTOR1</b>	IEC-320-C5
<b>VOLTAGE RATING</b>	100 - 250 VAC
<b>CONNECTOR GROUP</b>	UK plug C5
<b>CONNECTOR</b>	BS1363-UK plug IEC 320-C5

