



Eaton P070-010

IEC 309 to C19, Heavy-Duty Extension Cord - 16A, 250V, 16 AWG, 10 ft. (3.05 m), Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series extension cord
CATALOG NUMBER	P070-010
UPC	037332160706
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12.8 in
PRODUCT WIDTH	8.9 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	cUL Listed UL Listed

□□□□	
INPUT CURRENT -MAX	16 Ampere
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE	14° to 140°F (-10° to 60°C)
DEVICE COMPATIBILITY	Network Switch PDU Server UPS Router
AWG-SIZE	16
CABLE LENGTH	10 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	35% to 85% RH, Non-Condensing
OUTER CABLE DIAMETER	8.4mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	35% to 85% RH, Non-Condensing
WIRE SIZE (AWG) - MAX	1.29
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P070-010 IEC 309 to C19, Heavy-Duty Extension Cord, 10-ft. (3.05 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	High Voltage
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	16 AWG wire gauge manages high power levels required for larger equipment Heavy-duty extension cord replaces or upgrades standard manufacturer power cord Lifetime limited warranty (Worldwide) 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet Recommended for powering servers, routers and other high-output

□□

	network devices
PLUG COLOR	White Blue
SIDEA CONNECTOR1	IEC-320-C19
SIDEB CONNECTOR1	IEC-309 16A 2P+E
VOLTAGE RATING	100 VAC 250 VAC
CONNECTOR GROUP	C19 IEC-309
CONNECTOR	IEC-309 16A 2P+E IEC 320-C19
