




Eaton P137-06N-VGA

Keyspan Mini DisplayPort to Active VGA Adapter, Video Converter (M/F), White, 6-in. (15.24 cm)

□□□□

PRODUCT NAME	Eaton Tripp Lite series audio adapter
CATALOG NUMBER	P137-06N-VGA
UPC	037332158901
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.05 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS

TYPE	Video Adapter
OPERATING HUMIDITY RANGE	10% ~ 85% RH
STORAGE HUMIDITY RANGE	5% ~ 90% RH
COLOR	White
CONNECTOR TYPE	Video
PRODUCT FEATURES	TAA Compliant
PACKAGE CONTENTS	Mini-DisplayPort to Active VGA Adapter
PRODUCT HIGHLIGHTS	3-year limited warranty (Worldwide) Connect a VGA monitor to a Mac or PC with a Mini Displayport output Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p Compatible with Thunderbolt 1 and 2 ports on Mac computers Plug-and-play convenience—no drivers or software needed Converts both Single-Mode and Dual Mode (DP++) Displayport output
SIDEA CONNECTOR1	MINI DISPLAYPORT (MALE)
SIDEB CONNECTOR1	HD15 (FEMALE)
SIDEB CONNECTOR3	HD15 (FEMALE)
TECHNOLOGY	DisplayPort VGA / SVGA VGA/SVGA
FEATURES	Flex Center
CONNECTOR GROUP	DisplayPort VGA
CONNECTOR	Mini DisplayPort (male) HD15 (female)
CABLE LENGTH	0.5 Foot
OPERATING TEMPERATURE RANGE	32° to 158°F (0° to 70°C)
STORAGE TEMPERATURE RANGE	14° to 176°F (-10° to 80°C)
CABLE LENGTH RANGE	Up to 4ft (up to 1M)



TAA COMPLIANCE	Yes
----------------	-----