



□□□□

Eaton P2LM2W/UNV1 S891

Eaton Crouse-Hinds series Vaporgard Pro P2L LED light fixture, 0.12A, Warm white, AC drive, 50W HID or 150-200W incan equiv, 50/60 Hz, Without guard, Diffused glass lens, 1700 lm, Copper-free alum, Mounting module adapter, 120-277 Vac, 14W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Vaporgard Pro P2L LED light fixture
CATALOG NUMBER	P2LM2W/UNV1 S891
UPC	662276840942
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2.55 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	1.7 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	1700
COLOR TEMPERATURE	Warm white
MOUNTING METHOD	Mounting module adapter
VOLTAGE RATING	120-277 Vac
DRIVE TYPE	AC
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Diffused Glass
WATTAGE	14W
AMPERAGE RATING	0.12 A
MATERIAL	Copper-free aluminum
POWER FACTOR	> 0.9
GUARD	Without guard
EQUIVALENT LUMINAIRE	50W HID or 150-200W incandescent

□□

□□□□□

[IF 1884 - Vaporgard Pro Driver Modules - AC Version](#)

[IF 1627 - Vaporgard Pro P2L LED](#)

□□□□□□□

[Eaton Specification Sheet - P2LM2W/UNV1 S891](#)

[Crouse-Hinds series industrial LED lighting solutions](#)

□□□□

[Crouse-Hinds series Vaporgard Pro P2L/P3L LED brochure](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

□□□□

[Crouse-Hinds series Vaporgard Pro P2L/P3L LED catalog page](#)

□□□□

[Vaporgard Pro P2L Industrial LED Light Fixtures Canadian certification](#)

