



Eaton P351

Eaton Moeller series White moulded range (PREMERA) - Wiring Devices. TV outlet, coaxial, 1G

□□□□

PRODUCT NAME	Eaton Moeller series White moulded range (PREMERA) - Wiring devices
CATALOG NUMBER	P351
PRODUCT LENGTH/DEPTH	25 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	0.094 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	BS EN 50083-2 BS EN 60728-11 BS EN 60728-4 BS EN 60669-1



Powering Business Worldwide

□□□□

FEATURES	Antibacterial treatment Halogen free Insulated mounting
SURFACE FINISHING	Matt
TYPE	Communication outlet Premera white moulded
SURFACE PROTECTION	Untreated
MATERIAL QUALITY	Duroplast
MOUNTING METHOD	Flush mounted (plaster)
COLOR	White
FASTENING TYPE	Mounting with screw
CONNECTION TYPE	Screwed terminal
NUMBER OF GANGS	1
NUMBER OF SOCKET OUTLETS (SWITCHABLE)	0
NUMBER OF UNITS	1
RAL-NUMBER (AKIN)	9016
RECOMMENDED BACK BOX DEPTH - MIN	25 mm
FIXING CENTERS	60.3 mm
SPECIAL POWER SUPPLY	No special power supply
BUILT-IN INSTALLATION BOX DEPTH - MIN	25 mm
FAULT CURRENT RATING	1000 mA
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
NOMINAL CURRENT	0 A
NOMINAL VOLTAGE - MAX	0 V
NUMBER OF ACTIVE PINS (FLAT)	0
NUMBER OF ACTIVE PINS (ROUND)	0
NUMBER OF MODULES (MODULE SYSTEM)	0
NUMBER OF PHASES	1
DEGREE OF PROTECTION (IP)	IP20
FRONT PLATE COLOR/FINISHING	White
FRONT PLATE DEPTH	9 mm
IMPRINT/INDICATION	Other
FRONT PLATE MATERIAL	Urea

□□

	eaton-british-standard-wiring-accessories-poster-en-uk.pdf
□□□□	eaton-premera-mix-specification-guide-product-aid-pa081001en-en-gb.pdf
□□□□	eaton-wiring-accessories-and-single-phase-distribution-pg00400018u-en-gb.pdf

