



□□□□□

Eaton P3LM2W/DC1

Eaton Crouse-Hinds series Vaporgard Pro P2L LED, 3.0A, Warm white, DC drive, 50W HID or 150-200W incan equiv, 50/60 Hz, Without guard, Heat and impact resistant glass lens, 3000 lm, Copper-free alum, Mtg module adapter, 10-30 Vdc, 29W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Vaporgard Pro P2L LED light fixture
CATALOG NUMBER	P3LM2W/DC1
UPC	662276841901
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	2.55 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	1.7 lb

Certifications and compliances	
AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications	
LUMENS	3000
COLOR TEMPERATURE	Warm white
MOUNTING METHOD	Mounting module adapter
VOLTAGE RATING	10-30 Vdc
DRIVE TYPE	DC
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Heat and impact resistant glass
WATTAGE	29W
AMPERAGE RATING	3A
MATERIAL	Copper-free aluminum
POWER FACTOR	> 0.9
GUARD	Without guard
EQUIVALENT LUMINAIRE	50W HID or 150-200W incandescent

Links	
□□□□□	IF 1627 - Vaporgard Pro P2L LED
□□□□□□□□	Eaton Specification Sheet - P3LM2W/DC1
	Crouse-Hinds series industrial LED lighting solutions
□□□□	Crouse-Hinds series Vaporgard Pro P2L/P3L LED brochure
	Crouse-Hinds series Global LED lighting portfolio
□□□□	Crouse-Hinds series Vaporgard Pro P2L/P3L LED catalog page
□□□□	Vaporgard Pro P2L Industrial LED Light Fixtures Canadian certification

