



Eaton P415

Eaton Moeller series White moulded range (PREMERA) - Wiring Devices. Switched socket, 15A, 1G

□□□□

PRODUCT NAME	Eaton Moeller series White moulded range (PREMERA) - Wiring devices
CATALOG NUMBER	P415
PRODUCT LENGTH/DEPTH	40 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	0.084 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	BS 546



Powering Business Worldwide

□□□□

FEATURES	Protective contact Antibacterial treatment Halogen free
FITTED WITH:	Child-protection On/Off switch Loop through function
SURFACE FINISHING	Matt
SPECIAL FEATURES	Zinc Coated Steel with clear Passivation
TYPE	Premera White Moulded Sockets
AMPERAGE RATING	15A
VOLTAGE RATING	250 V AC
CONTACT MATERIAL	Silver Nickel
HEAD STYLE	Combination head
SURFACE PROTECTION	Untreated
MATERIAL QUALITY	Thermoplastic
SWITCH TYPE	Single-pole
MOUNTING METHOD	Flush mounted (plaster)
COLOR	White
FASTENING TYPE	Mounting with screw
CONNECTION TYPE	Screwed terminal
NUMBER OF GANGS	1
NUMBER OF SOCKET OUTLETS (SWITCHABLE)	1
NUMBER OF UNITS	1
RAL-NUMBER (AKIN)	0
RECOMMENDED BACK BOX DEPTH - MIN	35 mm
FIXING CENTERS	60.3 mm
BASE COLOR	Gray
BASE MATERIAL	Thermoplastic
SPECIAL POWER SUPPLY	No special power supply
TERMINAL MATERIAL	Brass
BUILT-IN INSTALLATION BOX DEPTH - MIN	35 mm
FAULT CURRENT RATING	250 mA
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
NOMINAL CURRENT	13 A
NOMINAL VOLTAGE - MAX	240 V

□□

	eaton-british-standard-wiring-accessories-poster-en-uk.pdf
□□□□	eaton-premera-mix-specification-guide-product-aid-pa081001en-en-gb.pdf
□□□□	eaton-wiring-accessories-and-single-phase-distribution-pg00400018u-en-gb.pdf

