



Eaton P421

Eaton Moeller series White moulded range (PREMERA) - Wiring Devices. Switch, 50A, 2p, 2G plate

□□□□

PRODUCT NAME	Eaton Moeller series White moulded range (PREMERA) - Wiring devices
CATALOG NUMBER	P421
PRODUCT LENGTH/DEPTH	50 mm
PRODUCT HEIGHT	148 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	0.188 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC 60669-1 BS EN 60669-1



Powering Business Worldwide

□□□□

FEATURES	Halogen free
SURFACE FINISHING	Matt
SPECIAL FEATURES	Terminal Screw Zinc Coated Steel with clear Passivation
TYPE	Premera white moulded Switch
AMPERAGE RATING	50 A
VOLTAGE RATING	250 V AC
CONTACT MATERIAL	Nickel Silver
HEAD STYLE	Combination head
ILLUMINATION	No
SURFACE PROTECTION	Untreated
MATERIAL QUALITY	Thermoplastic
ASSEMBLY ARRANGEMENT	Basic element with full cover plate
BASE COLOR	Gray
BASE MATERIAL	Thermoplastic
TERMINAL MATERIAL	Brass
BUILT-IN DEPTH	35 mm
BUILT-IN INSTALLATION BOX DEPTH - MIN	47 mm
NOMINAL VOLTAGE - MAX	250 V
NUMBER OF MODULES (MODULE SYSTEM)	0
NUMBER OF ROCKERS	1
SWITCH TYPE	Double pole
MOUNTING METHOD	Flush mounted (plaster)
DEGREE OF PROTECTION	IP20
FASTENING TYPE	Screw mounting
NUMBER OF GANGS	1
FIXING CENTERS	120.6 mm
FRONT PLATE COLOR/FINISHING	White
MATERIAL	Plastic Urea
FRONT PLATE DEPTH	9 mm
FRONT PLATE MATERIAL	Urea
FRONT PLATE/MODULE DIMENSIONS	148 mm x 86 mm
WIRING SYSTEM	2-pole switch
METHOD OF OPERATION	Rocker/button

□□

	eaton-british-standard-wiring-accessories-poster-en-uk.pdf
□□□□	eaton-premera-mix-specification-guide-product-aid-pa081001en-en-gb.pdf
□□□□	eaton-wiring-accessories-and-single-phase-distribution-pg00400018u-en-gb.pdf

FUNCTION LIGHTING	Other
ROCKER COLOR	White
COLOR	White
TERMINAL CAPACITY (LN AND E)	4 mm ² (3x) or 6 mm ² (2x) or 10 mm ² (1x)
CONNECTION TYPE	Screw terminal
LABEL SPACE/INFORMATION SURFACE	No
LIGHTING TYPE	Other
RAL-NUMBER (AKIN)	9016
RECOMMENDED BACK BOX DEPTH - MIN	47 mm
SWITCHING CURRENT OF FLUORESCENT LAMPS	45 Ampere AC/DC

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House
 30 Pembroke Road
 Dublin 4, □□□□
 Eaton.com

