



□□□□□

## Eaton P48G11S0518CUB

Eaton Mini-Power center, 5 kVA Mini Power Center 1 PH 480V to 120/240 Bolt-on breakers, Copper Windings 18 spaces

□□□□

|                             |                                                      |
|-----------------------------|------------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Mini-Power center                              |
| <b>CATALOG NUMBER</b>       | P48G11S0518CUB                                       |
| <b>UPC</b>                  | 786680225871                                         |
| <b>PRODUCT LENGTH/DEPTH</b> | 9.66 in                                              |
| <b>PRODUCT HEIGHT</b>       | 36.14 in                                             |
| <b>PRODUCT WIDTH</b>        | 12.56 in                                             |
| <b>PRODUCT WEIGHT</b>       | 110 lb                                               |
| <b>COMPLIANCES</b>          | NAFTA                                                |
| <b>CERTIFICATIONS</b>       | UL Listed<br>ANSI<br>IEEE Certified<br>CSA Certified |

|                    |                   |
|--------------------|-------------------|
| TYPE               | Mini-power center |
| COIL MATERIAL      | Copper            |
| FREQUENCY RATING   | 60 Hz             |
| KVA RATING         | 5 kVA             |
| KVA                | 5 kVA             |
| MOUNTING           | Wall Mount        |
| PHASE              | Single-phase      |
| PRIMARY VOLTAGE    | 480 V             |
| SECONDARY VOLTAGE  | 120/240 V         |
| SOUND LEVEL        | NEMA ST-20        |
| TEMPERATURE RISE   | 115 °C rise       |
| ENCLOSURE          | NEMA 3R           |
| FRAME              | 307               |
| INSULATION         | 180 °C            |
| MODIFICATION 1     | NEMA 3R           |
| TAP SIZE           | 2 at -5% FCBN     |
| VOLT AMPERE RATING | 5 kVA             |
| WEATHERSHIELD      | Not required      |
| WIRING CONNECTION  | M48G11DB          |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: