



Eaton P500-006

VGA High-Resolution RGB Coaxial Cable
(HD15 M/F)), 6 ft. (1.83 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P500-006
UPC	037332012296
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.57 lb
COMPLIANCES	RoHS

P500	
TYPE	Passive Cable
COLOR	Black
CABLE JACKET COLOR	Black
CONNECTOR TYPE	Video
PACKAGE CONTENTS	P500-006 VGA Coax High-Resolution Monitor Extension Cable (M/F), 6 ft.
PRODUCT HIGHLIGHTS	Made from mini-coax (RGB) and paired video wire Gold-plated connectors and contacts for maximum conductivity Integral strain relief protects against cable stress and cracking Lifetime limited warranty (Worldwide) Foil and braid shielding blocks hazardous EMI/RFI line noise Supports video resolutions up to 2048 x 1536, including 1080p
SIDEA CONNECTOR1	HD15 (MALE)
SIDEB CONNECTOR1	HD15 (FEMALE)
SIDEB CONNECTOR3	HD15 (FEMALE)
TECHNOLOGY	Coax VGA / SVGA VGA/SVGA
CONNECTOR GROUP	VGA
CONNECTOR	HD15 (male) HD15 (female)
CABLE LENGTH	6 Foot
CABLE TYPE	Passive
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)



