



Eaton P500-025

VGA High-Resolution RGB Coaxial Cable
(HD15 M/F)), 25 ft. (7.62 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P500-025
UPC	037332125170
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	12 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	CE Marked RoHS
CERTIFICATIONS	IEC/EN 62040-1

□□□□	
TYPE	Passive Cable
COLOR	Black
CABLE JACKET COLOR	Black
CONNECTOR TYPE	Video
PACKAGE CONTENTS	P500-025 VGA Coax High-Resolution Monitor Extension Cable (M/F), 25-ft. (7.62 m)
PRODUCT HIGHLIGHTS	Supports video resolutions up to 2048 x 1536, including 1080p Foil and braid shielding blocks hazardous EMI/RFI line noise Gold-plated connectors and contacts for maximum conductivity Lifetime limited warranty (Worldwide) Made from mini-coax (RGB) and paired video wire Integral strain relief protects against cable stress and cracking
SIDEA CONNECTOR1	HD15 (MALE)
SIDEB CONNECTOR1	HD15 (FEMALE)
SIDEB CONNECTOR3	HD15 (FEMALE)
TECHNOLOGY	VGA / SVGA Coax VGA/SVGA
CONNECTOR GROUP	VGA
CONNECTOR	HD15 (male) HD15 (female)
CABLE LENGTH	25 Foot
CABLE TYPE	Passive
CABLE LENGTH RANGE	20 - 50ft (6 - 15M)

□□

