



Eaton P502-006

VGA High-Resolution RGB Coaxial Cable
(HD15 M/M), 6 ft. (1.83 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P502-006
UPC	037332012319
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.58 lb
COMPLIANCES	RoHS

P502-006	
TYPE	Passive Cable
COLOR	Black
CABLE JACKET COLOR	Black
CONNECTOR TYPE	Video
PACKAGE CONTENTS	P502-006 VGA Coaxial High-Resolution Monitor Cable (M/M), 6 ft.
PRODUCT HIGHLIGHTS	Foil and braid shielding blocks hazardous EMI/RFI line noise Integral strain relief protects against cable stress and cracking Gold-plated connectors and contacts for maximum conductivity Made from mini-coaxial (RGB) and paired video wire Supports video resolutions up to 2048 x 1536, including 1080p Lifetime limited warranty (Worldwide)
SIDEA CONNECTOR1	HD15 (MALE)
SIDEB CONNECTOR1	HD15 (MALE)
SIDEB CONNECTOR3	HD15 (MALE)
TECHNOLOGY	VGA / SVGA Coax VGA/SVGA
CONNECTOR GROUP	VGA
CONNECTOR	HD15 (male)
CABLE LENGTH	6 Foot
CABLE TYPE	Passive
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)



