



Eaton P502-010

VGA High-Resolution RGB Coaxial Cable
(HD15 M/M), 10 ft. (3.05 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P502-010
UPC	037332146939
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	8 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	0.8 lb
COMPLIANCES	RoHS

□□□□	
TYPE	Passive Cable
RELATIVE HUMIDITY	0-90% non-condensing
COLOR	Black
CABLE JACKET COLOR	Black
CONNECTOR TYPE	Video
PACKAGE CONTENTS	P502-010 VGA Coaxial High-Resolution Monitor Cable (M/M), 10-ft. (3.05 m)
PRODUCT HIGHLIGHTS	Integral strain relief protects against cable stress and cracking Made from mini-coaxial (RGB) and paired video wire Lifetime limited warranty (Worldwide) Gold-plated connectors and contacts for maximum conductivity Foil and braid shielding blocks hazardous EMI/RFI line noise Supports video resolutions up to 2048 x 1536, including 1080p
SIDEA CONNECTOR1	HD15 (MALE)
SIDEB CONNECTOR1	HD15 (MALE)
SIDEB CONNECTOR3	HD15 (MALE)
TECHNOLOGY	Coax VGA / SVGA VGA/SVGA
CONNECTOR GROUP	VGA
CONNECTOR	HD15 (male)
CABLE LENGTH	10 Foot
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)

□□



© 2026 〇〇 〇〇〇〇〇〇〇〇