



Eaton P566-003

HDMI to DVI Cable, Digital Monitor Adapter and Video Converter (HDMI to DVI-D M/M), 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P566-003
UPC	037332181312
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.09 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS



Powering Business Worldwide

□□□□	
TYPE	Passive Cable
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PACKAGE CONTENTS	3-ft. (0.91 m) HDMI to DVI Gold Digital Video Cable (HDMI-M / DVI-M)
PRODUCT HIGHLIGHTS	Supports high-def video resolutions up to 1920 x 1080 @60Hz (1080p). This product is covered by a Lifetime Limited Warranty Lifetime limited warranty (Worldwide) Premium double shielded digital video cable protects against EMI/RFI noise. Gold plated connectors and contacts provide optimal signal transfer. Supports a bandwidth up to 5Gbps
CONTACT PLATING	Gold
PACKAGING TYPE	Polybag
HDCP SPECIFICATION	1.3
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	DVI-D SINGLE LINK (MALE)
SIDEB CONNECTOR3	DVI-D SINGLE LINK (MALE)
TECHNOLOGY	DVI HDMI
FEATURES	Flex Center
CONNECTOR GROUP	DVI HDMI
CONNECTOR	DVI-D single link (male) HDMI (male)
CABLE LENGTH	3 Foot
MAX SUPPORTED VIDEO RESOLUTION	1920 x 1200 (1080p)
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)

□□

STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
CABLE TYPE	Passive
MAX RESOLUTION	1080p
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
