




Eaton P568-003-8K6

8K HDMI Cable (M/M) - 8K 60 Hz / 4K 120 Hz, Dynamic HDR, 4:4:4, HDCP 2.2, Black, 3 ft.

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P568-003-8K6
UPC	037332254795
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.18 lb
COMPLIANCES	RoHS REACH CE Marked FCC Compliant UKCA WEEE Directive
CERTIFICATIONS	IEC/EN 62040-1

P568-003-8K6	
TYPE	Passive Cable
AUDIO SPECIFICATION	eARC
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Blue
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	3D Video Supported Consumer Electronics Control (CEC) Supported EDID Support Ethernet Support EDID Compatible HDR Support DSC Support
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	P568-003-8K6 HDMI Cable, 8K @ 60 Hz, M/M, Black, 3 ft. (0.9 m)
PRODUCT HIGHLIGHTS	Supports eARC for full-resolution object-based surround sound with no compression Supports UHD resolutions up to 8K @ 60 Hz (4:4:4) for heightened video quality Lifetime limited warranty (Worldwide) Supports Dynamic HDR for richer contrast and expanded color accuracy per frame Plug-and-play operation with no software required for easy, immediate installation
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDE A CONNECTOR1	HDMI (MALE)



SIDE B CONNECTOR1	HDMI (MALE)
SIDE B CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI
FEATURES	Flex Center
CONNECTOR GROUP	HDMI
BANDWIDTH	48 Gbps
CONNECTOR	HDMI (male)
SUPPORTED RESOLUTION	1280x720 (720p) 1920x1080 (1080p) 3840x2160 (4K) 7680 x 4320 (8K)
CABLE LENGTH	3 Foot
CABLE OUTER DIAMETER (OD)	7.3 mm
MAX SUPPORTED VIDEO RESOLUTION	7680 x 4320 (8K) @ 60Hz
MINIMUM BEND RADIUS	36.5mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
VIDEO INPUT	HDMI (MALE)
VIDEO OUTPUT	HDMI (MALE)
MAX RESOLUTION	8K/60
CABLE LENGTH RANGE	Up to 4ft (up to 1M)