



Eaton P568-003-FL

High-Speed HDMI Flat Cable, Digital Video with Audio, UHD 4K (M/M), Black, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P568-003-FL
UPC	037332137968
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.13 lb
COMPLIANCES	RoHS REACH

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	Stereo Audio
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Support Consumer Electronics Control (CEC) Supported
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	3-ft. (0.91 m) Flat High Speed HDMI Gold Cable
PRODUCT HIGHLIGHTS	Supports Ultra High Definition (UHD) 4K video resolutions Premium double-shielded digital audio/video cable Gold-plated connectors provide optimal signal transfer High Speed HDMI and HDCP compliant Lifetime limited warranty (Worldwide) Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.3
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI
FEATURES	Flex Center
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)
CABLE LENGTH	3 Foot

□□

CABLE OUTER DIAMETER (OD)	3.0*12.0mm
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 30Hz
MINIMUM BEND RADIUS	30mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	-40° to 176°F (-40° to 80°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/30
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
