



Eaton P568-010-SW

High-Speed HDMI Cable with Swivel Connectors, Digital Video with Audio, UHD 4K (M/M), 10 ft. (3.05 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P568-010-SW
UPC	037332153852
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.65 lb
COMPLIANCES	RoHS REACH

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	Stereo Audio
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	Consumer Electronics Control (CEC) Supported EDID Support
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Swivel
PACKAGE CONTENTS	10-ft. High Speed HDMI Gold Cable with Swivel Connectors
PRODUCT HIGHLIGHTS	High Speed HDMI and HDCP compliant Gold-plated connectors provide optimal signal transfer Lifetime limited warranty (Worldwide) Smooth and flexible 28 AWG jacket with protective mesh cover 180 degree swivel design is ideal for flat panel HDTV's and other hook-ups where space is limited Supports Ultra High Definition (UHD) 4K video resolutions Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.3
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)

□□	
----	--

TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)
CABLE LENGTH	10 Foot
CABLE OUTER DIAMETER (OD)	5.5 mm
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 30Hz
MINIMUM BEND RADIUS	55mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	-40° to 176°F (-40° to 80°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/30
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
