



Eaton P568-010

High-Speed HDMI Cable, Digital Video with Audio, UHD 4K (M/M), Black, 10 ft. (3.05 m)



| | |
|-----------------------------|-------------------------------|
| PRODUCT NAME | Eaton Tripp Lite series cable |
| CATALOG NUMBER | P568-010 |
| UPC | 037332122926 |
| PRODUCT LENGTH/DEPTH | 0.5 in |
| PRODUCT HEIGHT | 9 in |
| PRODUCT WIDTH | 7 in |
| PRODUCT WEIGHT | 0.36 lb |
| COMPLIANCES | REACH RoHS |



Powering Business Worldwide



| | |
|---------------------------------|--|
| TYPE | Passive Cable |
| AUDIO SPECIFICATION | Stereo Audio |
| OPERATING HUMIDITY RANGE | 10% to 85% RH, Non-Condensing |
| STORAGE HUMIDITY RANGE | 5% to 90% RH, Non-Condensing |
| COLOR | Black |
| CABLE JACKET RATING | VW-1 |
| CABLE JACKET COLOR | Black |
| CONNECTOR COLOR | Black |
| CONNECTOR PLATING | Gold |
| CONNECTOR TYPE | Video |
| PRODUCT FEATURES | Consumer Electronics Control (CEC) Supported EDID Support |
| CABLE JACKET MATERIAL | PVC |
| COLOR DEPTH | 24-bit True color 24-bit True Color |
| CONNECTOR STYLE | Straight |
| PACKAGE CONTENTS | 10-ft. (3.05 m) High Speed HDMI Gold Cable |
| PRODUCT HIGHLIGHTS | Gold-plated connectors provide optimal signal transfer High Speed HDMI and HDCP compliant Supports Ultra High Definition (UHD) 4K video resolutions Premium double-shielded digital audio/video cable Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter |
| CONTACT PLATING | Gold |
| CHROMA SUB SAMPLING | 4:4:4 |
| HDCP SPECIFICATION | 1.3 |
| SIDEA CONNECTOR1 | HDMI (MALE) |
| SIDEB CONNECTOR1 | HDMI (MALE) |
| SIDEB CONNECTOR3 | HDMI (MALE) |
| TECHNOLOGY | HDMI |
| FEATURES | Flex Center |
| CONNECTOR GROUP | HDMI |
| CONNECTOR | HDMI (male) |
| CABLE LENGTH | 10 Foot |
| CABLE OUTER DIAMETER | 5.5 mm |



| | |
|---------------------------------------|------------------------------|
| (OD) | |
| MAX SUPPORTED VIDEO RESOLUTION | 3840 x 2160 (4K) @ 30Hz |
| MINIMUM BEND RADIUS | 55mm |
| LED INDICATORS | 0 |
| OPERATING TEMPERATURE RANGE | 32° to 113°F (0° to 45°C) |
| STORAGE TEMPERATURE RANGE | -40° to 176°F (-40° to 80°C) |
| CABLE TYPE | Passive |
| SIGNAL TRANSMISSION | Bidirectional |
| MAX RESOLUTION | 4K/30 |
| CABLE LENGTH RANGE | 9 - 14ft (2 - 4M) |

| |
|-------|
| □□□□: |
| □□□□: |
| □□□: |
| □□: |



□□□□ Eaton House
 30 Pembroke Road
 Dublin 4, □□□□
 Eaton.com

