




Eaton P568-012

High-Speed HDMI Cable, Digital Video with Audio, UHD 4K (M/M), Black, 12 ft. (3.66 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P568-012
UPC	037332170019
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	8 in
PRODUCT WEIGHT	0.46 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	ARC
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	Consumer Electronics Control (CEC) Supported EDID Compatible EDID Support 3D Video Supported
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	12-ft. (3.66 m) High Speed HDMI Gold Cable
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) High Speed HDMI and HDCP compliant Gold-plated connectors provide optimal signal transfer Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter Premium double-shielded digital audio/video cable Supports Ultra High Definition (UHD) 4K video resolutions
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)



CABLE LENGTH	12 Foot
CABLE OUTER DIAMETER (OD)	7.3 mm
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 30Hz
MINIMUM BEND RADIUS	36.5mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/30
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
