



Eaton P568-016

High-Speed HDMI Cable, Digital Video with Audio, UHD 4K (M/M), Black, 16 ft. (4.88 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P568-016
UPC	037332122964
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	11 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.85 lb
COMPLIANCES	RoHS REACH

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	ARC
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	Consumer Electronics Control (CEC) Supported EDID Support EDID Compatible 3D Video Supported
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	16-ft. High Speed HDMI Gold Cable
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Gold-plated connectors provide optimal signal transfer High Speed HDMI and HDCP compliant Supports Ultra High Definition (UHD) 4K video resolutions Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter Premium double-shielded digital audio/video cable
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)

□□

CABLE LENGTH	16 Foot
CABLE OUTER DIAMETER (OD)	7.3 mm
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 30Hz
MINIMUM BEND RADIUS	36.5mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/30
CABLE LENGTH RANGE	14 - 20ft (4 - 6M)
