



Eaton P568-050

Standard-Speed HDMI Cable, Digital Video with Audio (M/M), Black, 50 ft. (15.24 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P568-050
UPC	037332137852
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	12 in
PRODUCT WEIGHT	2.2 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	ARC
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Compatible 3D Video Supported Consumer Electronics Control (CEC) Supported EDID Support
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	50-ft. Standard Speed HDMI Gold Cable
PRODUCT HIGHLIGHTS	Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter Gold-plated connectors provide optimal signal transfer Standard Speed HDMI and HDCP compliant Supports UHD Video resolutions up to 4K Bandwidth up to 10.2 Gbps - 4K resolution Lifetime limited warranty (Worldwide) Premium double-shielded digital audio/video cable
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI

□□

CONNECTOR	HDMI (male)
CABLE LENGTH	50 Foot
CABLE OUTER DIAMETER (OD)	7.3 mm
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 30Hz
MINIMUM BEND RADIUS	36.5mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/30
CABLE LENGTH RANGE	20 - 50ft (6 - 15M)



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

