



Eaton P568-100-HD

Standard-Speed HDMI Cable, 24 AWG High Definition, Digital Video with Audio Cable (M/M), 100 ft. (30.5 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P568-100-HD
UPC	037332153401
PRODUCT LENGTH/DEPTH	0.0001 in
PRODUCT HEIGHT	0.0001 in
PRODUCT WIDTH	0.0001 in
PRODUCT WEIGHT	0.0001 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	DTS-HD
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Compatible EDID Support Consumer Electronics Control (CEC) Supported
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	100-ft. (30.5 m) 24AWG High Definition Standard Speed HDMI Gold Cable (HDMI M/M)
PRODUCT HIGHLIGHTS	24AWG High Definition Standard Speed HDMI Gold cable Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter Lifetime limited warranty (Worldwide) Premium double-shielded digital audio/video cable Standard Speed HDMI and HDCP compliant Supports HD Video resolutions up to 1080p Gold-plated connectors provide optimal signal transfer
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI

□□

CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)
CABLE LENGTH	100 Foot
CABLE OUTER DIAMETER (OD)	9.0 mm
MAX SUPPORTED VIDEO RESOLUTION	1920 x 1200 (1080p)
MINIMUM BEND RADIUS	45mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	1080p
CABLE LENGTH RANGE	50ft and up (15M and up)
