



Eaton P569-000-FF-IND

4K HDMI Coupler with Ethernet (F/F),
Industrial High Speed, 4K 60 Hz, HDR, IP68
Rated, Dust Cap

□□□□

PRODUCT NAME	Eaton Tripp Lite series Industrial coupler
CATALOG NUMBER	P569-000-FF-IND
UPC	037332238443
PRODUCT LENGTH/DEPTH	7.5 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	5 in
PRODUCT WEIGHT	0.08 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH
CERTIFICATIONS	UL Listed

□□□□	
RELATIVE HUMIDITY	10% to 90% RH
COLOR	Black
CONNECTOR TYPE	Video
PRODUCT FEATURES	Industrial Grade TAA Compliant IP68 Rated
PACKAGE CONTENTS	P569-000-FF-IND 4K HDMI Coupler with Ethernet, 4K x 2K, Industrial High Speed
PRODUCT HIGHLIGHTS	Standard IP68 rating guarantees water resistance at depths up to 1.5 meters for up to 30 minutes. Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy Built to protect high-speed HDMI audio/video applications in harsh environments IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.* Lifetime limited warranty (Worldwide) Complies with HDCP 2.2 standards to display up-to- date 4K video content IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min. Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR3	HDMI (FEMALE)
TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (female)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
PROTECTION RATING	IP68
TAA COMPLIANCE	Yes



