



Eaton P569-003-IND

High-Speed HDMI Cable (M/M) - 4K 60 Hz, HDR, Industrial, IP68, Hooded Connector, Black, 3 ft.

□□□□

PRODUCT NAME	Eaton Tripp Lite series Industrial cable
CATALOG NUMBER	P569-003-IND
UPC	037332238436
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.223 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS FCC Compliant CE Marked REACH

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	ARC
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
RELATIVE HUMIDITY	0-90% non-condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Black
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	Industrial Grade Ethernet Support 3D Video Supported Consumer Electronics Control (CEC) Supported EDID Compatible Latching or Gripping Connector EDID Support HDR Support
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	P569-003-IND High-Speed HDMI Cable with Hooded Connector - M/M, Black, 3 ft.
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) IP68-rated cable resists dust and endure immersion in 1.5 m of water up to 60 min.* Built to protect HDMI audio/video and Ethernet applications in severe environments Standard IP68 rating guarantees water resistance at depths up to 1.5 meters for up to 30 minutes. Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy Complies with HDCP 2.2

□□	
----	--

	standards to display up-to-date 4K video content IP68-rated cable resists dust and endure immersion in 1.5 m of water up to 60 min. Supports UHD resolutions up to 4K (4:4:4) for crystal-clear video
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)
TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)
CABLE LENGTH	3 Foot
CABLE OUTER DIAMETER (OD)	7.3 mm
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	36.5mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	Up to 4ft (up to 1M)

□□□□:
□□□□:
□□□:
□□: