




Eaton P569-006-CERT

4K HDMI Cable with Ethernet (M/M) - 4K 60 Hz, Gripping Connectors, 6 ft.

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P569-006-CERT
UPC	037332199201
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7.2 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS

□□□□	
TYPE	Passive Cable
AUDIO SPECIFICATION	ARC
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
MATERIAL	PVC
CABLE JACKET COLOR	Black
CONNECTOR COLOR	Burgundy
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	Consumer Electronics Control (CEC) Supported HDR Support 3D Video Supported EDID Compatible EMI/RFI Line Noise Protection EDID Support Latching or Gripping Connector Ethernet Support
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	48-bit Deep color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	P569-006-CERT 4K HDMI Cable with Ethernet (M/M), 6 ft.
PRODUCT HIGHLIGHTS	Special high-grip plugs prevent accidental disconnections Supports UHD video resolutions up to 4K for crystal-clear video Ideal for connecting 4K televisions Tested for highest performance and ultra reliability Lifetime limited warranty (Worldwide)
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR1	HDMI (MALE)
SIDEB CONNECTOR3	HDMI (MALE)



TECHNOLOGY	HDMI
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (male)
CABLE LENGTH	6 Foot
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	36.5mm
LED INDICATORS	0
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

