



Eaton P580-003

DisplayPort Cable with Latching Connectors,
4K 60 Hz (M/M), Black, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P580-003
UPC	037332160485
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.13 lb
COMPLIANCES	REACH WEEE Directive RoHS

□□□□	
TYPE	Passive Cable
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Video
PRODUCT FEATURES	MST Support Latching or Gripping Connector 3D Video Supported EDID Compatible
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	DisplayPort Monitor Cable - 3ft
PRODUCT HIGHLIGHTS	Supports 1080p resolution Small footprint compared to VGA or DVI Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz Digital Video and Audio in one cable
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:2:0 4:2:2
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	DISPLAYPORT (MALE)
SIDEB CONNECTOR1	DISPLAYPORT (MALE)
SIDEB CONNECTOR3	DISPLAYPORT (MALE)
DISPLAYPORT SPECIFICATION	1.2
TECHNOLOGY	DisplayPort
FEATURES	Flex Center
CONNECTOR GROUP	DisplayPort
CONNECTOR	DisplayPort (male)
CABLE LENGTH	3 Foot
CABLE OUTER DIAMETER (OD)	6.0 mm

MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	60mm
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	-40° to 158°F (-40° to 70°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
