



Eaton P580-010

DisplayPort Cable with Latching Connectors,
4K 60 Hz (M/M), Black, 10 ft. (3.05 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P580-010
UPC	037332145956
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.34 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS WEEE Directive REACH

TYPE	Passive Cable
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Video
PRODUCT FEATURES	Latching or Gripping Connector MST Support EDID Compatible 3D Video Supported
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	DisplayPort to DisplayPort Cable 4K with Latches (M/M), 10 ft.
PRODUCT HIGHLIGHTS	Digital Video and Audio in one cable Lifetime limited warranty (Worldwide) Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz, including 1080p Small footprint compared to VGA or DVI
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:2:0 4:2:2
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	DISPLAYPORT (MALE)
SIDEB CONNECTOR1	DISPLAYPORT (MALE)
SIDEB CONNECTOR3	DISPLAYPORT (MALE)
DISPLAYPORT SPECIFICATION	1.2
TECHNOLOGY	DisplayPort
FEATURES	Flex Center
CONNECTOR GROUP	DisplayPort
CONNECTOR	DisplayPort (male)
CABLE LENGTH	10 Foot

CABLE OUTER DIAMETER (OD)	6.0 mm
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	60mm
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	-40° to 158°F (-40° to 70°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

